



386113



3-step switch, HVAC control

Technical Features

Voltage

Nominal voltage	250 - 250 V
-----------------	-------------

Electric current

Switching current	10 AX (100W LED (SBL))
-------------------	------------------------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Dimensions

Dimensions	71 x 71 mm
Depth	42 mm
Built-in depth flush-mounted boxes	35 mm

Materials

Material	Metal Plastic
----------	------------------

Architecture

Control/operation element	Rotative
---------------------------	----------

Texts

Switch mode	Without neutral position: 2-1-3
Type of connection	With screw terminals

Sustainability

RoHS conform	Yes
--------------	-----