



386103



**3-step switch, with neutral-position, HVAC control**

**Technical Features**

**Voltage**

Nominal voltage	250 - 250 V
Rated voltage	250 V

**Electric current**

Switching current	10 AX (100W LED (SBL))
-------------------	------------------------

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Electric current**

Rated current	10 A
---------------	------

**Dimensions**

Dimensions	71 x 71 mm
Depth	42 mm
Built-in depth flush-mounted boxes	35 mm

**Materials**

Material	Metal Plastic
----------	------------------

**Architecture**

Control/operation element	Rotative
---------------------------	----------

**Texts**

Switch mode	With neutral position: 0-1-2-3
Type of connection	With screw terminals

**Sustainability**

RoHS conform	Yes
--------------	-----