



386103



3-step switch, with neutral-position, HVAC control

Technical Features

Voltage

| | |
|-----------------|-------------|
| Nominal voltage | 250 - 250 V |
| Rated voltage | 250 V |

Electric current

| | |
|-------------------|------------------------|
| Switching current | 10 AX (100W LED (SBL)) |
|-------------------|------------------------|

Installation, mounting

| | |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Electric current

| | |
|---------------|------|
| Rated current | 10 A |
|---------------|------|

Dimensions

| | |
|------------------------------------|------------|
| Dimensions | 71 x 71 mm |
| Depth | 42 mm |
| Built-in depth flush-mounted boxes | 35 mm |

Materials

| | |
|----------|------------------|
| Material | Metal Plastic |
|----------|------------------|

Architecture

| | |
|---------------------------|----------|
| Control/operation element | Rotative |
|---------------------------|----------|

Texts

| | |
|--------------------|--------------------------------|
| Switch mode | With neutral position: 0-1-2-3 |
| Type of connection | With screw terminals |

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|