



VM018K

Enclosure, Design 30, 18 module, with DIN rail, metal, with KO

Technical Features

Installation, mounting

| | |
|----------------------------|------------------|
| Mounting on | Surface mounting |
| Suitable for outdoor usage | No |

Capacity

| | |
|-------------------|----|
| Number of modules | 18 |
|-------------------|----|

Electric current

| | |
|---------------|-------|
| Rated current | 100 A |
|---------------|-------|

Dimensions

| | |
|-----------------------|--------|
| Depth | 102 mm |
| Height | 240 mm |
| Width | 471 mm |
| Number of width units | 18 |

Cover, door

| | |
|---------------------------|----|
| Door/cover is transparent | No |
|---------------------------|----|

Materials

| | |
|----------|------------|
| RAL code | 9010 |
| Colour | Pure white |
| Material | Steel |

Equipment

| | |
|----------------|---|
| Number of rows | 1 |
|----------------|---|

Safety

| | |
|-------------------------------|---------------------|
| Impact resistance IK | IK05 |
| Ingress Protection (IP) class | IP2XC |
| Protection class | Isolation class III |

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |