



VA24D

Encl.,Volta,surface,2x12MOD,IP30,Version France

Technical Features

Installation, mounting

Mounting on Surface mounting

Electric current

Rated current 63 A

Power

Maximum power loss per cabinet at $\Delta T=20K$ 15 W

Equipment

Number of rows 2

With lock No

Has neutral terminal block No

Dimensions

Height 370 mm

Width 305 mm

Depth 96.50 mm

Cover, door

Number of cabinet doors 1

Dimensions

Number of width units 24

Cover, door

Door/cover is transparent No

Materials

Material Plastic

RAL code 9010

Colour Pure white

Equipment

Has mounting plate Yes

Materials

Ultraviolet-resistant Yes

Safety

Protection class Isolation class II

Impact resistance IK IK07

Ingress Protection (IP) class IP30

Locking type Snap on lock
Without lock

Glow wire test 750 °C

Sustainability

RoHS conform Yes