



JAE325

### Technical Features

#### Electric current

Rated current	250 A
Rated short-time withstand current Icw 1s IEC 60947	9 kA

#### Use conditions

Operating temperature	-5 - +40 °C
-----------------------	-------------

#### Frequency

Frequency	50-60 Hz
-----------	----------

#### Voltage

Rated insulation voltage Ui	800 V
Rated impulse withstand voltage Uimp	8 V

#### Safety

Ingress Protection (IP) class	IP41
-------------------------------	------

#### Dimensions

Height	400 mm
Width	375 mm
Depth	200 mm

#### Installation, mounting

Mounting on	Wall mounting
-------------	---------------

#### Sustainability

REACH-SVHC free	Yes
-----------------	-----