




20342089

Thermostat, NO contact,Cen. plate,f. heat.,rocker switch,ext.temp.sen.,R.1.3

Technical Features

Architecture

Control/operation element	Rotative
---------------------------	----------

Electric current

Rated current	16 A
---------------	------

Max. switching current	16 A
------------------------	------

Voltage

Nominal voltage	230 - 230 V
-----------------	-------------

Power supply

Supply voltage	230 V AC
----------------	----------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Settings

Comfort temperature setpoint	10 - 50 °C
------------------------------	------------

Materials

Colour	Polar white
--------	-------------

RAL code	9010
----------	------

Surface finish	Glossy
----------------	--------

Material	Metal Plastic
----------	------------------

Treatment	Untreated
-----------	-----------

Dimensions

Height	71 mm
--------	-------

Width	71 mm
-------	-------

Depth	50.20 mm
-------	----------

Screen

With display	No
--------------	----

Equipment

Switching temperature difference	1 K
----------------------------------	-----

Type of thermostat	Regulator of heating floor
--------------------	----------------------------

Type of probe	Floor heating probe
---------------	---------------------

With heater	Yes
-------------	-----

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Connection

Type of contacts	1NO
------------------	-----

Compatibility

Type of HVAC control	Heating
----------------------	---------

Use conditions

Energy efficiency class	I (1%)
-------------------------	--------

Texts

Installation mode	Without spreader claws
-------------------	------------------------

Type of connection	With screw terminals
--------------------	----------------------

Thermal re-circulation	With thermal return
------------------------	---------------------

Imprint	With imprint
---------	--------------

Junction	With separate connection for night lowering
----------	---

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes