



20342089

Thermostat, NO contact,Cen. plate,f. heat.,rocker switch,ext.temp.sen.,R.1.3

Technical Features

Architecture

Control/operation element	Rotative
---------------------------	----------

Electric current

Rated current	16 A
Max. switching current	16 A

Voltage

Nominal voltage	230 - 230 V
-----------------	-------------

Power supply

Supply voltage	230 V AC
----------------	----------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Settings

Comfort temperature setpoint	10 - 50 °C
------------------------------	------------

Materials

Colour	Polar white
RAL code	9010
Surface finish	Glossy
Material	Metal Plastic
Treatment	Untreated

Dimensions

Height	71 mm
Width	71 mm
Depth	50.20 mm

Screen

With display	No
--------------	----

Equipment

Switching temperature difference	1 K
Type of thermostat	Regulator of heating floor
Type of probe	Floor heating probe
With heater	Yes

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Connection

Type of contacts	1NO
------------------	-----

Compatibility

Type of HVAC control	Heating
----------------------	---------

Use conditions

Energy efficiency class	I (1%)
-------------------------	--------

Texts

Installation mode	Without spreader claws
Type of connection	With screw terminals
Thermal re-circulation	With thermal return
Imprint	With imprint
Junction	With separate connection for night lowering

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes
