



20342045

Thermostat,NO contact,Cen. plate,f. heat.,rocker switch,ext.temp.sen.,R.1.3,bl.

Technical Features

Architecture

Control/operation element Rotative

Electric current

Rated current 16 A

Max. switching current 16 A

Voltage

Nominal voltage 230 - 230 V

Power supply

Supply voltage 230 V AC

Frequency

Frequency 50 - 50 Hz

Settings

Comfort temperature setpoint 10 - 50 °C

Materials

Colour Black

RAL code 9005

Surface finish Glossy

Material Metal  
Plastic

Treatment Untreated

Dimensions

Height 71 mm

Width 71 mm

Depth 50.20 mm

Screen

With display No

Equipment

Switching temperature difference 1 K

Type of thermostat Regulator of heating floor

Type of probe Floor heating probe

Safety

Ingress Protection (IP) class IP20

Connection

Type of contacts 1NO

Compatibility

Type of HVAC control Heating

Use conditions

Energy efficiency class I (1%)

Texts

Installation mode Without spreader claws

Type of connection With screw terminals

Thermal re-circulation With thermal return

Imprint With imprint

Junction With separate connection for night lowering

Product Datasheet  
20342045

|                 |     |
|-----------------|-----|
| Sustainability  |     |
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |