



WRS51PSW

## 5A 1 Gang Unswitched Socket Polished Steel White Insert

### Technical Features

#### Voltage

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

#### Electric current

|               |     |
|---------------|-----|
| Rated current | 5 A |
|---------------|-----|

#### Materials

|                |                 |
|----------------|-----------------|
| Colour         | Silver          |
| Surface finish | Glossy          |
| Material       | Stainless steel |

#### Dimensions

|        |       |
|--------|-------|
| Height | 86 mm |
| Width  | 86 mm |
| Depth  | 25 mm |

#### Installation, mounting

|                               |                |
|-------------------------------|----------------|
| Mounting on                   | Flush mounting |
| Mounting-/Connection Position | Horizontal     |

#### Connectivity

|                    |                |
|--------------------|----------------|
| Type of connection | Screw terminal |
| Mounting type      | Screw mounting |

#### Equipment

|                                   |                  |
|-----------------------------------|------------------|
| Connector/plug type socket outlet | British Standard |
| Rotated central insert            | No               |
| With hinged lid                   | No               |
| With round protective earth pin   | Yes              |
| With signal lamp                  | No               |

#### Accessories

|                     |    |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

#### Capacity

|                   |   |
|-------------------|---|
| Number of modules | 0 |
|-------------------|---|

#### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

#### Functions

|                           |    |
|---------------------------|----|
| With orientation lighting | No |
| With function lighting    | No |

#### Identification

|              |    |
|--------------|----|
| With imprint | No |
|--------------|----|

#### Texts

|            |                             |
|------------|-----------------------------|
| Cover      | Full cover plate            |
| Wiring     | With earth connection       |
| Protection | Enhanced contact protection |

#### Sustainability

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |