



WMGS12BSB

20A 2 Way Single Pole Switch Brushed Steel Black Insert

Technical Features

Electric current

| | |
|-------------------|------|
| Switching current | 20 A |
|-------------------|------|

Installation, mounting

| | |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

Voltage

| | |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

Materials

| | |
|----------------|-----------------|
| Colour | Stainless steel |
| Surface finish | Matt |
| Material | Stainless steel |
| Treatment | Brushed |

Identification

| | |
|----------------------|--|
| Assembly arrangement | Basic element with central cover plate |
|----------------------|--|

Connectivity

| | |
|---------------|------------------|
| Mounting type | Snap-on mounting |
|---------------|------------------|

Controls and indicators

| | |
|-------------------|---|
| Number of buttons | 1 |
|-------------------|---|

Dimensions

| | |
|----------------|------------|
| Dimensions | 59 x 25 mm |
| Built-in depth | 13.10 mm |

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Architecture

| | |
|---------------------------|---------------|
| Control/operation element | Single rocker |
|---------------------------|---------------|

Electric current

| | |
|---------------|------|
| Rated current | 20 A |
|---------------|------|

Texts

| | |
|-------------|--|
| Lighting | Without lighting (cannot be illuminated) |
| Switch mode | 2-pole |

Sustainability

| | |
|-----------------|-----|
| Halogen free | Yes |
| REACH-SVHC free | Yes |
| RoHS conform | Yes |