



BE463N

**Earth leakage add-on block 4P 63A 100mA A Class**

**Technical Features**

**Voltage**

Rated operational voltage Ue	230 - 400 V
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	4000 V

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Electric current**

Rated residual operating current I <sub>dn</sub>	100 mA
Rated current	63 A

**Architecture**

Number of poles	4
Neutral position	Right

**Capacity**

Number of modules	3
-------------------	---

**Connectivity**

Down connection alignment for modular devices	Aligned terminal
---	------------------

**Dimensions**

Height	70 mm
Width	35 mm
Depth	92 mm