



HIC425E

ATS with energy management 4x 160A

Technical Features

Voltage

Rated operational voltage Ue	380 - 415 V
------------------------------	-------------

Electric current

Rated current	160 A
Rated conditional short-circuit current Icc with gl-gG fuses	100 kA

Power

Rated operational power under 400 V AC AC1	105000 W
--	----------

Architecture

Number of poles	4
Device construction type	Fixed built-in

Compatibility

Suitable for DIN Rail	Yes
Suitable for distribution board	Yes