



19640001

Push-button Crystal, TS Crystal, chrome glossy

Technical Features

Electric current

Momentary contact current 1.50 A

Voltage

Rated voltage 24 V

Architecture

Control/operation element Push button

Number of poles 1

Materials

Colour Chrome

Surface finish Glossy

Material Brass

Treatment Chrome plated
Untreated

Transparent No

Dimensions

Height 23 mm

Width 23 mm

Depth 23 mm

Built-in depth 13 mm

Controls and indicators

Number of buttons 1

Type of push button Single push button

With feedback signal contact No

Safety

Ingress Protection (IP) class IP20

Accessories

Has labelling field No

Use conditions

Operating temperature -20 - 60 °C

Texts

Imprint Without imprint

Installation mode For screw fastening

Switch mode Normally open contact

Type of connection With plug-in terminals