



19640001

Push-button Crystal, TS Crystal, chrome glossy

Technical Features

Electric current

Momentary contact current

1.50 A

Voltage

Rated voltage

24 V

Architecture

Control/operation element

Push button

Number of poles

1

Materials

Colour

Chrome

Surface finish

Glossy

Material

Brass

Treatment

Chrome plated
Untreated

Transparent

No

Dimensions

Height

23 mm

Width

23 mm

Depth

23 mm

Built-in depth

13 mm

Controls and indicators

Number of buttons

1

Type of push button

Single push button

With feedback signal contact

No

Safety

Ingress Protection (IP) class

IP20

Accessories

Has labelling field

No

Use conditions

Operating temperature

-20 - 60 °C

Texts

Imprint

Without imprint

Installation mode

For screw fastening

Switch mode

Normally open contact

Type of connection

With plug-in terminals