



FWU43D

FW flush encl. 3x4-rows, empty, IP30, classII, niche 657x815x115mm

### Technical Features

#### Dimensions

|                       |        |
|-----------------------|--------|
| Height                | 703 mm |
| Width                 | 853 mm |
| Depth                 | 125 mm |
| Thickness of sidewall | 1 mm   |

#### Safety

|                               |                    |
|-------------------------------|--------------------|
| Ingress Protection (IP) class | IP30               |
| Protection class              | Isolation class II |
| Locking type                  | Without lock       |
| Impact resistance IK          | IK09               |

#### Equipment

|                                 |   |
|---------------------------------|---|
| Number of section in width      | 3 |
| Number of flange plate openings | 6 |

#### Installation, mounting

|                            |                               |
|----------------------------|-------------------------------|
| Mounting on                | Flush mounting<br>Hollow wall |
| Suitable for outdoor usage | No                            |

#### Materials

|           |               |
|-----------|---------------|
| Colour    | Pure white    |
| RAL code  | 9010          |
| Treatment | Powder coated |
| Material  | Steel         |

#### Equipment

|                |   |
|----------------|---|
| Number of rows | 4 |
|----------------|---|

#### Cover, door

|                           |    |
|---------------------------|----|
| Number of cabinet doors   | 2  |
| Door/cover is transparent | No |

#### Electric current

|               |       |
|---------------|-------|
| Rated current | 125 A |
|---------------|-------|

#### Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|