




WXP4012

Plate gallery 2 gang horizontal 71mm moon glass material

Technical Features

Capacity

|                   |   |
|-------------------|---|
| Number of gangs   | 2 |
| Number of modules | 4 |

Materials

|                |                             |
|----------------|-----------------------------|
| Colour         | Traffic white               |
| RAL code       | 9016                        |
| Surface finish | Matt                        |
| Material       | Glass<br>Polycarbonate (PC) |

Dimensions

|        |          |
|--------|----------|
| Height | 87.70 mm |
| Width  | 163 mm   |
| Depth  | 9.30 mm  |

Accessories

|                     |    |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Installation, mounting

|                               |            |
|-------------------------------|------------|
| Mounting-/Connection Position | Horizontal |
|-------------------------------|------------|

Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP21 |
| Impact resistance IK          | IK05 |

Use conditions

|                       |             |
|-----------------------|-------------|
| Operating temperature | -10 - 35 °C |
|-----------------------|-------------|

Sustainability

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |