



FWU33S

FW flush encl. 3-rows 96 modules, IP30, classII, niche 507x815x115mm

Technical Features

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Flush mounting Hollow wall

Electric current

Rated current	125 A
---------------	-------

Equipment

Number of rails	9
Number of rows	3
Number of section in width	3
With lock	No
Has neutral terminal block	Yes

Capacity

Number of modules	108
-------------------	-----

Functions

With conduit inlets	Yes
---------------------	-----

Dimensions

Height	553 mm
Width	853 mm
Depth	125 mm
Built-in height	502 mm
Built-in width	810 mm

Cover, door

Number of cabinet doors	2
-------------------------	---

Dimensions

Built-in depth	112 mm
Number of width units	36

Cover, door

Type of handle	Hinged pattern handle
Door/cover is transparent	No

Connection

Number of conduit inlets	6
--------------------------	---

Materials

Material	Steel
RAL code	9010
Colour	Pure white

Equipment

Has earthing terminal block	Yes
Has mounting plate	No

Safety

Protection class	Isolation class II
Impact resistance IK	IK09
Ingress Protection (IP) class	IP30
Locking type	Without lock

Sustainability

RoHS conform	Yes
--------------	-----