



459410



**Aerial soc. 4hole single box, DC-permeable**

**Technical Features**

**Connectivity**

Mounting type	Screw mounting
---------------	----------------

**Attenuation**

Tap loss at 2150 MHz	2 dB
Tap loss at 860 MHz	2 dB

**Connection**

Connector/plug type	End socket
---------------------	------------

**Frequency**

Frequency bandwidth	5 - 2400 MHz
Broadband technology	5 - 2400 MHz

**Equipment**

Number of outputs	4
-------------------	---

**Materials**

Material	Metal
----------	-------

**Dimensions**

Depth	27.20 mm
Built-in depth	40 mm

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Texts**

Function	Suitable for HDTV
Voltage	DC voltage conducting
Type of connection	With screw terminals
Supporting plate/supporting ring	External eyelets on the supporting ring can be broken off for round designs

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes