



WGMHDCAS

16AX DND&MUR SWITCH W/ LED (INDOOR), AS

Technical Features

<strong>Electric current</strong>	
Switching current	16 A
<strong>Voltage</strong>	
Rated voltage	250 V
<strong>Frequency</strong>	
Frequency	50 - 60 Hz
<strong>Materials</strong>	
Colour	Aurora silver
Surface finish	Matt
Treatment	Varnished
<strong>Controls and indicators</strong>	
Number of buttons	2
<strong>Dimensions</strong>	
Dimensions	86 x 86 mm
<strong>Safety</strong>	
Ingress Protection (IP) class	IP20
<strong>Architecture</strong>	
Control/operation element	Double rocker
<strong>Electric current</strong>	
Rated current	16 A
<strong>Sustainability</strong>	
REACH-SVHC free	Yes
RoHS conform	Yes