



47287103

SCHUKO soc. out. 45°, K.5, al., matt, lacq.

Technical Features

Electric current

Rated current 16 A

Voltage

Rated voltage 250 V

Nominal voltage 250 - 250 V

Frequency

Frequency 50 - 60 Hz

Materials

Colour Aluminium

RAL code 9006

Surface finish Matt

Material Thermoplastic

Treatment Untreated
Varnished

Dimensions

Height 71 mm

Width 71 mm

Number of units 1

Built-in depth 32 mm

Connection

Connector/plug type Plug clamp

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Plug-in connection

Mounting type Screw mounting
Claw mounting

Equipment

Connector/plug type socket outlet SCHUKO

Rotated central insert Yes

With hinged lid No

With round protective earth pin No

With signal lamp No

With lock No

Accessories

Has labelling field Yes

Capacity

Number of modules 1

Safety

With enhanced contact protection No

Impact resistance IK IK05

Ingress Protection (IP) class IP20

Functions

With orientation lighting No

With function lighting No

Texts

Imprint Without imprint

Cover Central cover plate

Texts	
Protection	Without enhanced contact protection
Type of connection	With plug-in terminals
Suitable for	
K.x	
Sustainability	
RoHS conform	Yes