



KDN380B

**Insulated busbar 3P 80A fork 16mm<sup>2</sup> 57M**

**Technical Features**

**Electric current**

Rated current 80 A

**Architecture**

Number of poles 3

**Dimensions**

Length 1000 mm

**Voltage**

Rated impulse withstand voltage Uimp 4500 V

Rated operational voltage Ue 230 - 400 V

**Connection**

Cross-section rigid conductor 16 mm<sup>2</sup>

Connector/plug type Phase busbar with fork

**Capacity**

Number of modules 57

**Sustainability**

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes