



KDN380B

**Insulated busbar 3P 80A fork 16mm<sup>2</sup> 57M**

**Technical Features**

**Electric current**

Rated current	80 A
---------------	------

**Architecture**

Number of poles	3
Type of pole	3P

**Dimensions**

Length	1000 mm
--------	---------

**Voltage**

Rated impulse withstand voltage Uimp	4500 V
Rated operational voltage Ue	230 - 400 V

**Connection**

Cross-section rigid conductor	16 mm <sup>2</sup>
Connector/plug type	Phase busbar with fork

**Capacity**

Number of modules	57
-------------------	----

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes