Product Datasheet
BE425N



BE425N

Earth leakage add-on block 4P 25A 100mA A Class

Technical Features

Voltage	
Rated operational voltage Ue	230 - 400 V
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	4000 V
Frequency	
Frequency	50 - 50 Hz
Electric current	
Rated residual operating current Idn	100 mA
Rated current	25 A
Architecture	
Number of poles	4
Neutral position	Right
Capacity	
Number of modules	2
Installation, mounting	
Nominal tightening torque	2.20 - 2.20 Nm
Nominal tightening torque down terminal	2.20 - 2.20 Nm
Connectivity	
Down connection alignment for modular devices	Aligned terminal
Dimensions	
Height	70 mm
Width	35 mm
Depth	92 mm