



VF312TY

Small distributor,golf,flush,3row,36M,QC-terminal,N+PE,transparent door

**Technical Features**

**Voltage**

Nominal voltage	400 - 400 V
-----------------	-------------

**Installation, mounting**

Suitable for outdoor usage	No
Mounting on	Flush mounting

**Electric current**

Rated current	63 A
---------------	------

**Equipment**

Number of rails	3
Number of rows	3
Number of section in width	1
With lock	No
Has neutral terminal block	Yes

**Capacity**

Number of modules	36
-------------------	----

**Functions**

With conduit inlets	Yes
---------------------	-----

**Dimensions**

Height	543 mm
Width	352 mm
Depth	97.50 mm
Built-in height	507 mm
Built-in width	318 mm

**Cover, door**

Number of cabinet doors	1
-------------------------	---

**Dimensions**

Built-in depth	72 mm
----------------	-------

**Cover, door**

Number of locks	0
-----------------	---

**Dimensions**

Number of width units	12
-----------------------	----

**Cover, door**

Door/cover is transparent	Yes
---------------------------	-----

**Materials**

Material	Plastic
RAL code	9010
Colour	Pure white

**Equipment**

Has earthing terminal block	Yes
Has mounting plate	No

**Materials**

Ultraviolet-resistant	No
-----------------------	----

**Safety**

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP40

**Safety**

Locking type	Snap on lock Without lock
Glow wire test	850 °C

**Sustainability**

RoHS conform	Yes
--------------	-----