



VF312PM

Small distributor,golf,flush,3row,36M,IP40,MS-terminal,N+PE,white door

### Technical Features

#### Voltage

|                 |             |
|-----------------|-------------|
| Nominal voltage | 400 - 400 V |
|-----------------|-------------|

#### Installation, mounting

|                            |                |
|----------------------------|----------------|
| Suitable for outdoor usage | No             |
| Mounting on                | Flush mounting |

#### Electric current

|               |      |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

#### Equipment

|                            |     |
|----------------------------|-----|
| Number of rails            | 3   |
| Number of rows             | 3   |
| Number of section in width | 1   |
| With lock                  | No  |
| Has neutral terminal block | Yes |

#### Capacity

|                   |    |
|-------------------|----|
| Number of modules | 36 |
|-------------------|----|

#### Functions

|                     |     |
|---------------------|-----|
| With conduit inlets | Yes |
|---------------------|-----|

#### Dimensions

|                 |          |
|-----------------|----------|
| Height          | 543 mm   |
| Width           | 352 mm   |
| Depth           | 97.50 mm |
| Built-in height | 507 mm   |
| Built-in width  | 318 mm   |

#### Cover, door

|                         |   |
|-------------------------|---|
| Number of cabinet doors | 1 |
|-------------------------|---|

#### Dimensions

|                |       |
|----------------|-------|
| Built-in depth | 72 mm |
|----------------|-------|

#### Cover, door

|                 |   |
|-----------------|---|
| Number of locks | 0 |
|-----------------|---|

#### Dimensions

|                       |    |
|-----------------------|----|
| Number of width units | 12 |
|-----------------------|----|

#### Cover, door

|                           |    |
|---------------------------|----|
| Door/cover is transparent | No |
|---------------------------|----|

#### Materials

|          |            |
|----------|------------|
| Material | Plastic    |
| RAL code | 9010       |
| Colour   | Pure white |

#### Equipment

|                             |     |
|-----------------------------|-----|
| Has earthing terminal block | Yes |
| Has mounting plate          | No  |

#### Materials

|                       |    |
|-----------------------|----|
| Ultraviolet-resistant | No |
|-----------------------|----|

#### Safety

|                               |                    |
|-------------------------------|--------------------|
| Protection class              | Isolation class II |
| Impact resistance IK          | IK07               |
| Ingress Protection (IP) class | IP40               |

**Safety**

|                |              |
|----------------|--------------|
| Locking type   | Snap on lock |
|                | Without lock |
| Glow wire test | 650 °C       |

**Sustainability**

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|