



WMSS820

2 Gang Double Pole Switched Socket Dual Earth Outboard Rockers

Technical Features

Electric current

Rated current	13 A
---------------	------

Voltage

Rated voltage	250 V
---------------	-------

Nominal voltage	250 - 250 V
-----------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	White
--------	-------

Surface finish	Glossy
----------------	--------

Material	Urea formaldehyde
----------	-------------------

Treatment	Untreated
-----------	-----------

Dimensions

Height	86 mm
--------	-------

Width	146 mm
-------	--------

Depth	29.50 mm
-------	----------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Mounting-/Connection Position	Horizontal
-------------------------------	------------

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Mounting type	Screw mounting
---------------	----------------

Equipment

Connector/plug type socket outlet	British Standard
-----------------------------------	------------------

Rotated central insert	No
------------------------	----

With hinged lid	No
-----------------	----

With round protective earth pin	No
---------------------------------	----

With signal lamp	No
------------------	----

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	0
-------------------	---

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Functions

With orientation lighting	No
---------------------------	----

With function lighting	No
------------------------	----

Texts

Imprint	Without imprint
---------	-----------------

Cover	Full cover plate
-------	------------------

Wiring	With double earth connection
--------	------------------------------

Protection	Enhanced contact protection
------------	-----------------------------

Sustainability

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----