




WMINDREDB

Indicator Module RED

Technical Features

Frequency

Frequency	50 - 60 Hz
-----------	------------

Lighting

Type of lamp	LED
--------------	-----

Materials

Colour	Red
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Untreated

Dimensions

Height	60 mm
Width	25 mm
Depth	24 mm

Connectivity

Mounting type	Clamp mounting
---------------	----------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Use conditions

Operating temperature	-15 - 40 °C
-----------------------	-------------

Texts

Imprint	Without imprint
---------	-----------------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes