



EN145

Interface relay VLV/ LV

Technical Features

Electric current

Rated current	5 A
Max. power (cos phi 0,6)	5 A

Frequency

Frequency	50 - 60 Hz
-----------	------------

Capacity

Number of modules	1
-------------------	---

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Voltage

Command voltage AC	10 - 26 V
--------------------	-----------

Sustainability

RoHS conform	Yes
--------------	-----

Illustrations | Drawings

