



KB380B

Insulated busbar 3P 80A prong 16mm² 57M

Technical Features

Electric current

Rated current 80 A

Architecture

Number of poles 3

Dimensions

Length 1000 mm

Voltage

Rated impulse withstand voltage Uimp 4000 V

Rated operational voltage Ue 230 - 400 V

Connection

Cross-section rigid conductor 16 mm²

Connector/plug type Phase busbar with pin

Capacity

Number of modules 57

Sustainability

REACH-SVHC free Yes

RoHS conform Yes