



11309909

Cover plate f.rot. dimmer/potentiometer, setting knob, S.1, p.white matt plastic

Technical Features

Architecture

Control/operation element	Rotative
---------------------------	----------

Materials

Colour	Polar white
RAL code	9010
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

Dimensions

Height	80.30 mm
Width	80.40 mm
Depth	11.60 mm
Diameter axis	4 mm

Connectivity

Mounting type	Screw mounting
---------------	----------------

Equipment

Monitoring window/light outlet	No
--------------------------------	----

Accessories

Has labelling field	No
---------------------	----

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Texts

Imprint	Without imprint
Installation mode	For screw fastening

Suitable for

S.x/B.x	
---------	--

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes