

# Product Datasheet

## BDC380E



BDC380E

### Earth leakage add-on-block 3P 125A 30mA type AC

#### Technical Features

##### Electric current

Rated current	125 A
Rated residual operating current I <sub>dn</sub>	30 mA

##### Architecture

Number of poles	3
-----------------	---

##### Safety

Residual current type	AC
-----------------------	----

##### Voltage

Rated insulation voltage U <sub>i</sub>	500 V
Rated impulse withstand voltage U <sub>imp</sub>	6000 V

##### Connection

Cross-section of input and output with screws, for massive conductors	10 - 70 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	10 - 50 mm <sup>2</sup>

##### Connectivity

Type of connection	Screw terminal
Down connection alignment for modular devices	Aligned terminal

##### Dimensions

Height	103 mm
Width	187 mm
Depth	69 mm

#### Illustrations | Drawings

