



941952501

SCHUKO sock. outl., enh. cont. prot., screw term, Int. mod. inserts, brown matt

Technical Features

Electric current

Rated current	16 A
---------------	------

Voltage

Rated voltage	250 V
Nominal voltage	250 - 250 V

Frequency

Frequency	50 - 50 Hz
-----------	------------

Materials

Colour	Brown
RAL code	8017
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

Dimensions

Height	55.50 mm
Width	55.50 mm
Number of units	1
Built-in depth flush-mounted boxes	32 mm

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Connectivity

Type of connection	Screw terminal
Mounting type	Built in installation Screw mounting

Equipment

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	1
-------------------	---

Safety

With enhanced contact protection	Yes
Impact resistance IK	IK05
Ingress Protection (IP) class	IP20

Functions

With orientation lighting	No
With function lighting	No

Texts

Imprint	Without imprint
Cover	Central cover plate
Protection	Enhanced contact protection
Type of connection	With screw terminals

Suitable for

integro
