



VT36F

36M 3Row DIN Flush Metal BOX, No Door

Technical Features

Voltage

Nominal voltage	230 - 415 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

Equipment

Number of rails	3
Number of rows	3

Capacity

Number of modules	36
-------------------	----

Dimensions

Height	654 mm
Width	414 mm
Depth	10 mm
Built-in width	364 mm
Built-in depth	60 mm

Cover, door

Number of locks	0
-----------------	---

Dimensions

Number of width units	12
-----------------------	----

Cover, door

Door/cover is transparent	No
---------------------------	----

Connection

Number of conduit inlets	16
--------------------------	----

Connectivity

Mounting type	Screw mounting
---------------	----------------

Materials

Material	Steel
RAL code	9002
Colour	Grey white

Equipment

Has mounting plate	No
--------------------	----

Safety

Protection class	Isolation class I
Impact resistance IK	IK05

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes