



GBA501611ALU

Install. trunking-Base Alu 50161,anodised.

Technical Features

Dimensions

| | |
|--------|---------|
| Height | 56 mm |
| Width | 162 mm |
| Length | 2000 mm |

Cover, door

| | |
|--------------------------|-------|
| Number of mountable lids | 3 |
| Cover width 1 | 45 mm |
| Cover width 2 | 45 mm |
| Cover width 3 | 45 mm |

Dimensions

| | |
|---------------------|-----------------------------|
| Inner cross-section | 8000 - 8000 mm ² |
|---------------------|-----------------------------|

Capacity

| | |
|--|----|
| Max. number of cables (Ø11 mm, 50% filled, with devices) | 30 |
| Max. number of cables (Ø11mm, 50% filled, without devices) | 57 |

Compatibility

| | |
|---------------------------------------|------------|
| Device installation compatible format | 47 x 45 mm |
|---------------------------------------|------------|

Installation, mounting

| | |
|------------------|----|
| Base perforation | No |
|------------------|----|

Materials

| | |
|-----------|-----------|
| Material | Aluminium |
| Treatment | Anodised |
| Colour | Aluminium |

Safety

| | |
|-------------------------------|------|
| Impact resistance IK | IK07 |
| Ingress Protection (IP) class | IP40 |

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5 - 90 °C |
|-----------------------|------------|

Connectivity

| | |
|-------------------|--------------------------------|
| Trunking coupling | Couplers as separate reference |
|-------------------|--------------------------------|

Equipment

| | |
|-------------------------------------|-----|
| Cable retaining clip included | No |
| Number of cable retainers per meter | 0 |
| With protective film | Yes |

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |

Illustrations | Drawings

