



HNT041JR

Moulded Case Circuit Breaker h3+ P250 LSI 4P4D N0-50-100% 40A 40kA FTC

Technical Features

Electric current

Rated current	40 A
Rated ultimate short-circuit breaking capacity I _{cu} under 230 V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity I _{cu} under 240 V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity I _{cu} under 400 V AC IEC 60947-2	40 kA
Rated ultimate short-circuit breaking capacity I _{cu} under 415 V AC IEC 60947-2	40 kA
Breaking capacity on 1-pole for AC 230 V IEC 60947-2	2.50 kA
Breaking capacity on 1-pole for AC 400 V IEC 60947-2	2.50 kA

Architecture

Number of poles	4
Control/operation element	Toggle
Device construction type	Fixed built-in
Neutral position	Left

Electric current

Rated ultimate short-circuit breaking capacity I _{cu} under 690 V AC IEC 60947-2	6 kA
Rated service breaking capacity I _{cs} under 220 V AC according to IEC 60947-2	50 kA
Rated service breaking capacity I _{cs} under 230 V AC according to IEC 60947-2	50 kA
Rated service breaking capacity I _{cs} under 240 V AC according to IEC 60947-2	50 kA
Rated service breaking capacity I _{cs} under 380 V AC according to IEC 60947-2	40 kA
Rated service breaking capacity I _{cs} under 400 V AC according to IEC 60947-2	40 kA
Rated service breaking capacity I _{cs} under 415 V AC according to IEC 60947-2	40 kA
Rated service breaking capacity I _{cs} under 690 V AC according to IEC 60947-2	6 kA
Rated current 10°C according to IEC 60947	40 A
Rated current 15°C according to IEC 60947	40 A
Rated current 20°C according to IEC 60947	40 A
Rated current 25°C according to IEC 60947	40 A
Rated current 30°C according to IEC 60947	40 A
Rated current at 35°C according to IEC 60947	40 A
Rated current at 40°C according to IEC 60947	40 A
Rated current 45°C according to IEC 60947	40 A
Rated current 50°C according to IEC 60947	40 A
Rated current 55°C according to IEC 60947	40 A
Rated current at 60°C according to IEC 60947	40 A
Rated current 70°C according to IEC 60947	40 A
Rated current 65°C according to IEC 60947	40 A

Settings

Ir1 current dial setting	16 A
	18 A
	20 A
	22 A
	25 A
	28 A
	32 A
	34 A
	37 A
	40 A
Adjustment range short-term delayed short-circuit release	21.9 - 400.0 A

Frequency

Frequency	50 - 60 Hz
-----------	------------

Installation, mounting

Nominal tightening torque	12 - 12 Nm
Mounting-/Connection Position	Front

Voltage

Rated impulse withstand voltage Uimp	8000 V
Rated insulation voltage Ui	800 V
Rated operational voltage Ue	220 - 690 V

Functions

Trip unit	LSI
-----------	-----

Power

Total power loss under IN	1.14 W
Power loss per pole at In	0.38 W

Endurance

Electric endurance in number of cycles	10000
Number of mechanical operations	40000

Equipment

Number of auxiliary contacts as change-over contact	0
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0

Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

Use conditions

Operating temperature	-25 - 70 °C
-----------------------	-------------

Connection

Cross-section flexible conductor	35 - 150 mm ²
----------------------------------	--------------------------

Cover, door

Interlockable	Yes
---------------	-----

Connection

Cross-section rigid conductor	35 - 185 mm ²
Connector/plug type	Terminal

Cable

Cable material	Copper Aluminium
----------------	---------------------

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	3
--	---

Dimensions

Height	165 mm
Width	140 mm
Depth	97 mm

Controls and indicators

Motor drive integrated	No
------------------------	----

Compatibility

Suitable for DIN Rail	No
Compatible with RDC AOB	Yes
Suitable for distribution board	Yes

Power supply

Position power supply	Bidirectional
-----------------------	---------------

Electrical protection

Long-time overload protection (ltd): delay (tr)	0.5 s
	1.5 s
	2.5 s
	5 s
	7.5 s
	9 s
	10 s
	12 s
	14 s
	16 s
Short-time protection (std): current (lsd)	1.5
	2
	3
	4
	5
	6
	7
	8
	10
Short-time protection (std): delay (tsd)	50 ms
	100 ms
	200 ms
	300 ms
	400 ms
Instantaneous protection (li): dial setting coefficient	3
	4
	5
	6
	7
	8
	10
	12
	15

Sustainability

RoHS conform	Yes
--------------	-----