



16409909

Relay switch centre plate for hotel card, S.1/B.3/B.7, p. white, matt, plastic

Technical Features

Electric current

Switching current	10 A
Momentary contact current	10 A

Voltage

Rated voltage	230 V
---------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Architecture

Control/operation element	Hotel card
Number of poles	1

Power

230 V incandescent and halogen lamp	1500 W
Fluorescent lamps in duo circuit	1500 W

Materials

Colour	Polar white
Surface finish	Matt
Material	Metal Plastic
Treatment	Untreated
Transparent	No

Dimensions

Height	71 mm
Width	71 mm
Depth	57.30 mm
Built-in depth	32 mm
Built-in depth flush-mounted boxes	35 mm

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Controls and indicators

Number of buttons	0
With feedback signal contact	No

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Accessories

Has labelling field	No
---------------------	----

Use conditions

Operating temperature	-5 - 50 °C
-----------------------	------------

Texts

Imprint	With imprint "Hotelcard"
Installation mode	With spreader claws
Lighting	For illumination
Switch mode	1-pole
Type of connection	With screw-in lift terminals

Suitable for

S.x/B.x	
---------	--

Sustainability	
RoHS conform	Yes