



WPSS82R

2 Gang Double Pole Switched Socket with Outboard Red Rocker & Back Box with KOs

Technical Features

Electric current

Rated current 13 A

Frequency

Frequency 50 - 60 Hz

Materials

Colour Grey

Surface finish Glossy

Material Steel

Treatment Epoxy

Dimensions

Height 86 mm

Width 146 mm

Depth 53.20 mm

Installation, mounting

Mounting on Flush mounting

Mounting-/Connection Position Horizontal

Connectivity

Type of connection Screw terminal

Mounting type Screw mounting

Equipment

Connector/plug type socket outlet British Standard

Rotated central insert No

With hinged lid No

With round protective earth pin No

With signal lamp No

Accessories

Has labelling field No

Capacity

Number of modules 0

Safety

Ingress Protection (IP) class IP20

Functions

With orientation lighting No

With function lighting No

Identification

With imprint No

Texts

Cover Full cover plate

Wiring With double earth connection

Protection Enhanced contact protection

Sustainability

REACH-SVHC free Yes

RoHS conform Yes