



4202



Soc.out. earth. contact+hinged cover US/CAN NEMA 5-15 R,screw, flushmtd IP44

Technical Features

Voltage

Rated voltage 125 V

Electric current

Rated current 15 A

Frequency

Frequency 50 - 50 Hz

Materials

Colour White

RAL code 1013

Surface finish Glossy

Material Thermoplastic

Treatment Untreated

Dimensions

Height 71 mm

Width 71 mm

Built-in depth 19 mm

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Screw terminal

Mounting type Screw mounting

Equipment

Connector/plug type socket outlet NEMA

Rotated central insert No

With hinged lid Yes

With signal lamp No

With lock No

Accessories

Has labelling field No

Cover, door

Type of lid Self-closing hinged cover

Capacity

Number of modules 1

Safety

With enhanced contact protection No

Impact resistance IK IK05

Ingress Protection (IP) class IP44

Functions

With orientation lighting No

With function lighting No

Texts

Cover Central cover plate

Protection Without enhanced contact protection

Type of connection With screw terminals

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes
