



TYA670W

Gateway KNX-DALI, tunable white, 4 modules

Technical Features

Equipment

| | |
|------------|-----|
| Web server | Yes |
|------------|-----|

Voltage

| | |
|----------------------------|-------------|
| Operating voltage | 240 - 240 V |
| Operating voltage over bus | 21 - 32 V |

Connectivity

| | |
|--|-----------------------------|
| Type of interface bus system/media gateway | Light system interface/DALI |
|--|-----------------------------|

Settings

| | |
|------------------------------|-----|
| Supported configuration mode | ETS |
|------------------------------|-----|

Power

| | |
|----------------------|---------|
| Power consumption VA | 0.15 VA |
|----------------------|---------|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP30 |
|-------------------------------|------|

Equipment

| | |
|--------------------|---|
| Number of channels | 1 |
|--------------------|---|

Use conditions

| | |
|-----------------------|-----------|
| Operating temperature | 5 - 45 °C |
|-----------------------|-----------|

Controls and indicators

| | |
|---------------------|-----|
| With LED indication | Yes |
|---------------------|-----|

Dimensions

| | |
|-----------------------|------------|
| Width | 72 mm |
| Dimensions | 90 x 72 mm |
| Depth | 70 mm |
| Number of width units | 4 |

Connection

| | |
|---------------------|------------------------|
| Connector/plug type | DRA (DIN-rail Adapter) |
|---------------------|------------------------|

Texts

| | |
|--------------------|--|
| Voltage | As DALI master and power supply for DALI devices |
| Type of connection | With screw terminals |

Sustainability

| | |
|-----------------|-----|
| Halogen free | Yes |
| REACH-SVHC free | Yes |
| RoHS conform | Yes |