



EC40600CT

Current Transformer with RJ45 output BGUK 3-Phase 600A/330mV Class 1 pitch 45mm

Technical Features

Functions

Accuracy class	1
----------------	---

Dimensions

Height	90 mm
Width	140 mm
Depth	54 mm
Height of opening	31 mm
Width of opening	31 mm

Connectivity

Type of connection	Plug-in connection
--------------------	--------------------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Voltage

Rated insulation voltage Ui	3000 V
-----------------------------	--------

Use conditions

Operating temperature	-25 - 50 °C
Storage/transport temperature	-40 - 85 °C

Electric current

Max. intensity of primary	600 A
---------------------------	-------

Installation, mounting

Mounting on	Busbar Cable
-------------	-----------------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes