



FS24G

Steel enclosure, Univers, IP41, CL1, 1850x1050x400 mm

Technical Features

Dimensions

Height	1850 mm
Width	1050 mm
Depth	400 mm
Thickness of sidewall	1.50 mm

Safety

Ingress Protection (IP) class	IP41
Protection class	Isolation class I
Locking type	Double lock bar Without lock
Impact resistance IK	IK07

Equipment

Number of section in width	4
Number of flange plate openings	8

Installation, mounting

Mounting on	Floor mounting Wall mounting
Suitable for outdoor usage	No

Materials

Colour	Light grey
RAL code	7035
Treatment	Powder coated
Material	Steel

Equipment

Number of rows	12
----------------	----

Materials

Surface finish	Matt
----------------	------

Cover, door

Number of cabinet doors	2
Number of locks	1
Door/cover is transparent	No

Electric current

Rated current	800 A
---------------	-------

Voltage

Nominal voltage	690 - 690 V
-----------------	-------------

Sustainability

RoHS conform	Yes
--------------	-----