



47413512



**SCHUKO soc.out. hinged cover surface-mtd, W.1, p. white, matt, plastic**

**Technical Features**

**Voltage**

Rated voltage 250 V

**Electric current**

Rated current 16 A

**Use conditions**

Operating temperature -15 - 30 °C

**Frequency**

Frequency 50 - 60 Hz

**Materials**

Colour Polar white  
RAL code 9010  
Surface finish Matt  
Material Thermoplastic  
Treatment Untreated

**Dimensions**

Height 76 mm  
Width 76 mm  
Depth 63 mm  
Built-in depth flush-mounted boxes 0 mm  
Height of P-touch band for labelling field 12 mm

**Installation, mounting**

Mounting on Surface mounting

**Connectivity**

Type of connection Plug-in connection  
Mounting type Screw mounting  
Claw mounting

**Equipment**

Connector/plug type socket outlet SCHUKO  
Rotated central insert No  
With hinged lid Yes  
With round protective earth pin No  
With signal lamp No  
With lock No

**Accessories**

Has labelling field Yes

**Cover, door**

Type of lid Self-closing hinged cover, can be arrested in end position

**Capacity**

Number of modules 1

**Safety**

With enhanced contact protection No  
Impact resistance IK IK05  
Ingress Protection (IP) class IP55

**Functions**

With orientation lighting No  
With function lighting No

---

**Identification**

---

With imprint	No
--------------	----

---

**Texts**

---

Cover	Complete housing
-------	------------------

---

Protection	Without enhanced contact protection
------------	-------------------------------------

---

Type of connection	With plug-in terminals
--------------------	------------------------

---

Labelling	With labelling field
-----------	----------------------

---

Terminal	With Wago clip-in 2-wire connection terminal for wiring With two clip-in places for Wago 2-wire connection terminals in the housing floor
----------	--

---

**Sustainability**

---

Halogen free	Yes
--------------	-----

---

RoHS conform	Yes
--------------	-----

---