



VM012

Enclosure, Design 30, 12 module, with DIN rail, metal

Technical Features

Installation, mounting

Mounting on	Surface mounting
Suitable for outdoor usage	No

Capacity

Number of modules	12
-------------------	----

Electric current

Rated current	100 A
---------------	-------

Dimensions

Depth	102 mm
Height	240 mm
Width	292 mm
Number of width units	12

Cover, door

Door/cover is transparent	No
---------------------------	----

Materials

RAL code	9010
Colour	Pure white
Material	Steel

Equipment

Number of rows	1
----------------	---

Safety

Impact resistance IK	IK05
Ingress Protection (IP) class	IP2XC
Protection class	Isolation class III

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes