



47517104

SCHUKO soc.out. hinged cover, enhanced contact prot., K.5, steel, matt finish

Technical Features

Electric current

Rated current	16 A
---------------	------

Voltage

Rated voltage	250 V
Nominal voltage	250 - 250 V

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Stainless steel
RAL code	9022
Surface finish	Matt
Material	Metal
	Stainless steel

Dimensions

Height	71 mm
Width	71 mm
Number of units	1
Built-in depth flush-mounted boxes	35 mm
Built-in depth	32 mm

Connection

Connector/plug type	Plug clamp
---------------------	------------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Connectivity

Type of connection	Plug-in connection
Mounting type	Screw mounting
	Claw mounting

Equipment

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	No
With signal lamp	No
With lock	No

Accessories

Has labelling field	No
---------------------	----

Cover, door

Type of lid	Hinged cover falls back
-------------	-------------------------

Capacity

Number of modules	1
-------------------	---

Safety

With enhanced contact protection	Yes
Impact resistance IK	IK07
Ingress Protection (IP) class	IP20

Functions

With orientation lighting	No
With function lighting	No

Texts

Imprint	Without imprint
Cover	Central cover plate
Type of connection	With plug-in terminals

Suitable for

K.x

Sustainability

RoHS conform	Yes
--------------	-----