



TYA628C



Output device for 8 shutters or blinds 230V~

Technical Features

Settings

Supported configuration mode	ETS
------------------------------	-----

Connectivity

With bus system KNX radio	No
---------------------------	----

Installation, mounting

Mounting on	DIN rail
-------------	----------

Materials

Colour	Light grey
--------	------------

Equipment

With switch for manual switch	Yes
-------------------------------	-----

Electric current

Rated current	6 A
Max. switching current	6 A

Voltage

Operating voltage over bus	21 - 32 V
----------------------------	-----------

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Connection

Cross-section flexible conductor	0.75 - 2.5 mm ²
Cross-section rigid conductor	0.75 - 2.5 mm ²

Capacity

Number of modules	6
-------------------	---

Texts

Function	With safety functions e.g. for wind, rain, alarm With positioning function for blind and lamella position With sun shade function
Type of connection	With quickconnect plug-in terminals
Operating mode	Operating mode can be set for roller shutter/awning

Sustainability

RoHS conform	Yes
--------------	-----