



TYA628C



**Output device for 8 shutters or blinds 230V~**

**Technical Features**

**Settings**

Supported configuration mode ETS

**Connectivity**

With bus system KNX radio No

**Installation, mounting**

Mounting on DIN rail

**Materials**

Colour Light grey

**Equipment**

With switch for manual switch Yes

**Electric current**

Rated current 6 A

Max. switching current 6 A

**Voltage**

Operating voltage over bus 21 - 32 V

**Use conditions**

Operating temperature -5 - 45 °C

**Connection**

Cross-section flexible conductor 0.75 - 2.5 mm<sup>2</sup>

Cross-section rigid conductor 0.75 - 2.5 mm<sup>2</sup>

**Capacity**

Number of modules 6

**Texts**

Function With safety functions e.g. for wind, rain, alarm  
With positioning function for blind and lamella position  
With sun shade function

Type of connection With quickconnect plug-in terminals

Operating mode Operating mode can be set for roller shutter/awning

**Sustainability**

REACH-SVHC free Yes