



TYA670D

**Gateway KNX/EIB-DALI, 4 modules**

**Technical Features**

**Equipment**

Web server	Yes
------------	-----

**Voltage**

Operating voltage	240 - 240 V
Operating voltage over bus	21 - 32 V

**Connectivity**

Type of interface bus system/media gateway	Light system interface/DALI
--	-----------------------------

**Settings**

Supported configuration mode	ETS
------------------------------	-----

**Power**

Power consumption VA	0.15 VA
----------------------	---------

**Safety**

Ingress Protection (IP) class	IP30
-------------------------------	------

**Equipment**

Number of channels	1
--------------------	---

**Use conditions**

Operating temperature	5 - 45 °C
-----------------------	-----------

**Controls and indicators**

With LED indication	Yes
---------------------	-----

**Dimensions**

Width	72 mm
Dimensions	90 x 72 mm
Depth	70 mm
Number of width units	4

**Texts**

Voltage	As DALI master and power supply for DALI devices
Type of connection	With screw terminals

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes