



75662726



Push-butt. 2gang, w. lab. fields, room therm., displ., Q.x, anthr. velvety

Technical Features

Installation, mounting

Mounting on Flush mounting

Use conditions

Operating temperature -5 - 45 °C

Functions

With room temperature controller Yes

Dimensions

Built-in depth	21.40 mm
Built-in depth flush-mounted boxes	25 mm
Height	70.90 mm
Width	70.90 mm
Depth	34.80 mm

Equipment

Number of actuation points 6

Controls and indicators

With LED indication Yes

Materials

Colour	Anthracite
RAL code	7021
Material	Thermoplastic
Surface finish	Velvety

Accessories

Has labelling field Yes

Screen

With display Yes

Texts

Function	For switch, push-button, dimmer, blind and thermostat functions With valve protection function
Operating mode	Controller operating modes: comfort, standby, night and frost/heat protection mode
Protection	With dismantling protection
Temperature	Temperature measurement via internal and/or external sensor with mean value formation

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes