


75662729



Push-button 2gang, w. labelling fields, room therm., displ., Q.x, pw velvety

Technical Features

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Functions

With room temperature controller	Yes
----------------------------------	-----

Dimensions

Built-in depth	21.40 mm
Built-in depth flush-mounted boxes	25 mm
Height	70.90 mm
Width	70.90 mm
Depth	34.80 mm

Equipment

Number of actuation points	6
----------------------------	---

Controls and indicators

With LED indication	Yes
---------------------	-----

Materials

Colour	Polar white
RAL code	9010
Material	Thermoplastic
Surface finish	Velvety

Accessories

Has labelling field	Yes
---------------------	-----

Screen

With display	Yes
--------------	-----

Texts

Function	For switch, push-button, dimmer, blind and thermostat functions With valve protection function
Operating mode	Controller operating modes: comfort, standby, night and frost/heat protection mode
Protection	With dismantling protection
Temperature	Temperature measurement via internal and/or external sensor with mean value formation

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes